

SMART SOLUTIONS DISPENSE

Industrial process automation meets easy operation

- + innovative software "SIA"
- + intuitive operation via tablet
- + control via symbols & gestures, graphical visualisation
- + no previous knowledge necessary for the operator
- + set-up process possible without programmer
- + quick & easy changeover
- + easy maintenance thanks to modular inserts & maintenance door
- + precise setup using live image
- + worldwide support by qualified staff
- + short delivery time
- + continuous software development & regular updates


Technical description:

- precise pulse or spray dosing of various fluids & pastes
- intuitive set-up and operation using "SIA" software via tablet
- precise definition of the processing points thanks to camera support
- manual component feeding and removal

Application areas:

- Pre & small series
- Laboratory testing & prototyping
- Seasonal operations
- AfterSales (spare & wear parts)
- Universities & Institutes





Technical data

Cell size (including rollers):	1000 x 1000 x 2200mm
Article weight:	< 5kg
Article dimensions:	< 200 x 200 x 200mm
Movement range X,Y-table:	200 x 300mm
Z-stroke:	200mm
Pulse frequency:	60Hz
Dosing functions:	Pulse dosing, spray dosing
Electrical connection:	CEE plug 400 - 480V, 50 - 60Hz, 16A
Safety:	Security camera in the operator area
Maintenance:	Maintenance rear door incl. safety contact
Switch cabinet:	Module inserts under the table

